



Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White

By Bryant
Catalog # [7596ER](#)



Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Midget Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Flanged Receptacle
UPC	781786671454

Dimensions

Dimensions	2.06 in x 1.62 in x 1.17 in
Display Size	Midget Locking
Height	1.17 in
Length	2.06 in
Width	1.62 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Nema Rating	ML-2R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [7594NP - Locking Devices, Bryant Midget Locking, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, ML-2P, Screw Terminal, Black](#)
- [7595MB - Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 3-Wire Grounding, ML-2P, Screw Terminal, Black & White](#)
- [7400BCR - Straight Blade Devices, Locking Devices, Accessories, Weatherproof Boot for Midget Devices, For 15A, 2-Pole 2-Wire, Yellow](#)
- [7593NC - Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7596ER-SPEC-EN | REV 7/2023