



Locking Devices, Industrial, Female Connector Body, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant
Catalog # 7764



Locking Devices, Industrial, Female Connector Body, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Heavy Duty Connector-For Replacement Use
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786629882

Dimensions

Dimensions	6.50 in x 2.56 in x 2.56 in
Display Size	Standard Sized Product
Height	2.56 in
Length	6.50 in
Width	2.56 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Conductor Range	#6 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-22 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)
- [7968 - Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A 250V DC/600V AC, Non-NEMA, Screw Terminal, Galvanized Steel, With Lift Cover](#)
- [7717B - Locking Devices, Accessories, Weatherproof Boot, Nylon Connector Body, For 50A Black](#)
- [7765 - Locking Devices, Industrial, Male Plug, 50A 250V/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7764-SPEC-EN | REV 7/2023