



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 3-Phase Wye 277/480V AC, Watertight

By Bryant  
Catalog # 520B7W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire Grounding, Screw Terminals, Red, Watertight

## Features

- Industrial Grade
- Male Flanged Inlet
- 20A 3-Phase Wye 277/480V AC
- 4- Pole 5-Wire Grounding
- Screw Terminals

## Application

High Ampacity Watertight Connections

## General

Catalog Number	520B7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C

Type	w/o impact
UPC	Inlet 781786251731

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	3 Phase Y 277/480 V
Voltage Rating Description	3 Phase Y 277/480V
Wattage	9600

## Conductor Related

Number Of Wires	5-Wire
-----------------	--------

## Product Assets

[Specifications - 520B7W](#)