



Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A 250V DC/600V AC, Non-NEMA, Screw Terminal, Galvanized Steel, With Lift Cover

By Bryant
Catalog # 7968



Locking Devices, Industrial, Flanged Inlet with Lift Cover and Gasket, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel, With Lift Cover

Application

Extra Heavy Duty Industrial

General

Color	Metallic
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Single Flanged - For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786672208

Dimensions

Dimensions	2.77 in x 3.50 in x 3.50 in
Display Size	Standard Sized Product
Height	3.50 in
Length	2.77 in
Width	3.50 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-22 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7764 - Locking Devices, Industrial, Female Connector Body, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White](#)
[7780 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Black Polycarbonate](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7968-SPEC-EN | REV 7/2023