

IEC Pin and Sleeve, Watertight Plug, 100/125 A, 120/208 VAC

By Bryant
Catalog # [BRY5100P9W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Male, Plug, 100/125 A 120/208 VAC, 4-POLE 5-WIRE, Blue, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection

Application

High Ampacity Connections

General

Catalog Number	BRY5100P9W
Color	Blue
Environmental Conditions	IP67
Ingress Protection	IP67
Insulation	Insulated Body
Material	PBT
Mounting Type	Cord Mounted
Number Of Poles	4-POLE
Series	Watertight IP67
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plug
UPC	781786782495

Electrical Ratings

Amperage Rating	100/125 A
Current / Amperage Rating	100/125 A
Dielectric Strength	Withstand 3000V AC
Voltage - Maximum	600 VAC
Voltage Rating	120/208 VAC
Voltage Rating Description	120/208 VAC

Conductor Related

Number Of Wires	5-WIRE
Wire Size	#4 AWG to #1 AWG

Certifications And Compliance

Industry Standard(s)	All constructions are UL Listed & cUL Listed, FileE14633, UL1686 Standard for Pin & Sleeve Configurations, VDE, CE
Nema Rating	Non-NEMA

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - BRY K-11 Catalog Page](#)
[Catalog Page - BRY K-5 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Sales Drawings - M14030](#)
[Specifications - BRYANT_BRY5100P9W_spec](#)