



Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Blue, Single Pack

By Bryant
Catalog # BRY5362BU



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Blue, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|--|
| Catalog Number | BRY5362BU |
| Color | Blue |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Traditional Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Extra Heavy Duty |
| Style | Finder Groove Face |
| Type | Duplex Receptacle |
| UPC | 781786005259 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.54 in x 1.16 in |
| Display Size | Standard Sized Product |
| Height | 1.16 in |

| | |
|--------|---------|
| Length | 3.28 in |
| Weight | 0.2 lb |
| Width | 1.54 in |

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 2500 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - BRY A-8 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - BRYANT® Wiring Devices](#)
[Specifications - BRY5362BU](#)