



Straight Blade Devices, Plug Strip, 6) Receptacles, Non-Metallic Body, 6' Cord

By Bryant
Catalog # [BRY6PPS](#)

Straight Blade Devices, Plug Strip, 6) Receptacles, Non-Metallic Body , 6' Cord



Application

6 Outlet, Heavy Duty Devices

General

Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet Series	Straight Blade 5-15R Economy Power Strips (no SPD)
Type	Non-Metallic
UPC	781786141605

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cord Length	6 ft
-------------	------

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Catalog Page - Bryant D-5 Catalog page](#)
[Catalog Page - Bryant B-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Surge Protection Devices](#)

Related Products

[BRY7PS1050M - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 7\) Receptacles, Metallic Body, 1050 Joules, 6' Cord, Modem Protection](#)
[T1254SI6A - Straight Blade Devices, Receptacle Cordsets, TVSS Receptacle, Commercial/Industrial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, 6' Cord](#)
[BRY8PS2100D - Bryant Wiring Devices, Cord and Cable Reels, Commercial Cord Reel, 25'With HBL5969VBLK Connector Body, Yellow.](#)
[BRY6MPS - Straight Blade Devices, Plug Strip, 6\) Receptacles, Metallic Body, 6' Cord](#)
[BRY6PS350 - Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6\) Receptacles, Metallic Body, 350 Joules, 6' Cord](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-BRY6PPS-SPEC-EN | REV 7/2023