



Locking Devices, Industrial, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black and White

By Bryant
Catalog # 70520NP



Locking Devices, Industrial, Male Nylon Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786688629

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L5-20P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Healthcare Solutions](#)
[Literature - General Literature - Pool Pump Receptacle Kit](#)
[Literature - General Literature - Power Disruption Solutions](#)
[Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-70520NP-SPEC-EN | REV 4/2023