



Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light

By Bryant
Catalog # DR15NLWH



Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light, White.

Performance

- Electrical - Color Temperature - 3400K - 3600K
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Electrical - LED Energy Consumed - 0.5 watt
- Electrical - Light Output - 0.5 Lumens
- Electrical - Rating - 15A, 125VAC Only
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	DR15NLWH
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Automatic Self-grounding Staple - Stainless steel • Base - Nylon • Face - Nylon • Lens - Polycarbonate • Mounting Screws - Zinc Plated Steel • Mounting Strap - Galvanized Steel • Power Contacts - .030 in. (.8) Brass • Terminal Screws - Plated Steel

UPC

- Wire Clamp - .062 in. (1.6) Nickel plated steel
- 783585541341

Dimensions

Dimensions	3.29 in x 1.15 in x 1.29 in
Display Size	Standard Sized Product
Height	1.29 in
Length	3.29 in
Width	1.15 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire Grounding
-----------------	------------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

Catalog Page - WDK A-31 Catalog Page
Catalog Page - WDK Z-5 Catalog Page
Catalogs - WDK Catalog Full 2024

Catalogs - Bryant Full Line Catalog
Literature - Residential Catalog
Specifications - DR15NLWH



©2024 Hubbell Incorporated. All rights reserved
BRY-DR15NLWH-SPEC-EN | REV 10/2024