



Locking Devices, Industrial, Female Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, Black and White

By Bryant
Catalog # 70620NC



Locking Devices, Industrial, Female Nylon Connector Body, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, Black/White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

General

Application	Heavy Duty Industrial
Catalog Number	70620NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786689299

Dimensions

Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L6-20R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	2000

Product Assets

- [Catalog Page - BRY H-8 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Healthcare Solutions](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)
- [Literature - General Literature - Power Disruption Solutions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-70620NC-SPEC-EN | REV 6/2024