



Locking Devices, Industrial, Flush Receptacle, 30A 120V AC 400Hz, 2-Pole 3-Wire Grounding, FSL2R, Screw Terminal, Black

By Bryant
Catalog # FSL2FR



Locking Devices, Industrial, Flush Receptacle, 30A 120V AC 400Hz, 2-Pole 3-Wire Grounding, NEMA FSL2, Screw Terminal, Black.

Features

- Combination back and side wiring terminals accept #14 through #8 AWG solid or stranded conductors
- Heavy duty mounting straps are nickel-plated to resist corrosion, wide width design assures secure assembly
- NEMA rating and configuration are molded into face for easy identification
- One-piece, rivetless copper-alloy contact design reduces heat buildup and provides secure blade retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	FSL2FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786638259

Dimensions

Dimensions	3.28 in x 1.71 in x 1.14 in
Display Size	Standard Sized Product
Height	1.14 in
Length	3.28 in
Width	1.71 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	120 V
Voltage Rating Description	120V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	FSL2-R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY Q-18 Catalog Page](#)
- [Catalog Page - BRY H-14 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - FSL2FR](#)