



# FSP Adapter Panel, 24-Fiber, LC Quad, 24-Port, Loaded with 6 Adapters, Phosphor Bronze, Aqua

By Bryant  
Catalog # [FSPLCQM6AQ](#)

FSP Adapter Panel, 24-Fiber, LC Quad, 24-Port, Loaded with 6 Adapters, Phosphor Bronze, Aqua



## Features

- Premium Quality and High Performance Design

## Application

Interconnect

## General

Color	Aqua
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103877

## Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

## Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• TIA-568-C.3</li><li>• TIA-604-FOCIS</li></ul>
----------------------	---

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-FSPLCQM6AQ-SPEC-EN | REV 7/2023