



# Power Protection Products, GFCI Circuit Breakers, Industrial, Single Pole, 40A 120V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black

By Bryant  
Catalog # [GFMDCB120401P](#)



Power Protection Products, GFCI Circuit Breakers, Industrial, Single Pole, 40A 120V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black

## Features

- Industrial
- Single Pole
- 40A 120V AC
- GFCI Circuit Breaker Sensing Modules
- 4-6 mA Trip Level

## Application

Heavy Duty Industrial Commercial

## General

Catalog Number	GFMDCB120401P
Color	Black
EU RoHS Indicator	No
Enclosure Type	Toggle
Environmental Conditions	NEMA 4X with Supplied Gasket
Frame	Single Phase
Item Type	Circuit Breaker
Material	Composite
Number Of Poles	None
OEM Brand Name	Hubbell Bryant
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Industrial
Style	1 Pole
Timing Response	1-Pole
Type	Circuit Breaker
UPC	781786450202

## Dimensions

Width 0.73 in

## Electrical Ratings

Amperage Rating	40 A
Connectivity	None
Current / Amperage Rating	40 A
Current Rating	40 A
Frequency Rating	80% of Full Rating Continuous
Interrupt Rating	40 A
Phase	60Hz
Trip Range	.025 Seconds in
Trip Type	Standard
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

## Conductor Related

Wire Size Terminal Screws

## Logistics

Carton Quantity 36

## Product Assets

[Catalog Page - BRY C-7 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Ground Fault Sensing Module Specifications - GFMDCB120401P](#)