



Locking Devices, Industrial, Flanged Inlet, 20A 250V, 3-Pole 4- Wire Grounding, L14-20P, Screw Terminal, White, With Weatherproof Cover

By Bryant
Catalog # 71420MBWP



Locking Devices, Industrial, Flanged Inlet, 20A 125/250V AC,
3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, White,
With Weatherproof Cover

Application

Extra Heavy Duty Industrial

General

Color	White
Environmental Conditions	Weather Resistant
Insulation	Insulated Body
Item Type	20A Weather Protective Power Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Weatherprotective
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786695177

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L14-20P
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-9 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-71420MBWP-SPEC-EN | REV 5/2023