

Single Pole Products, Female Receptacle, Threaded Stud Termination, 150 Amp Series, White

By Bryant
Catalog # [HBL15FRSW](#)



Single Pole Products, Female Receptacle, Threaded Stud Termination, 150 Amp Series, White

Features

- Threaded Stud Termination
- 150 Amp Series
- White

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15FRSW
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Female Receptacle
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none"> • Base Compound - Thermoplastic Elastomer (TPE) • Contact Material - Brass • Mounting Hole - 3x Ø .20" • Retaining Screw Material - Nylon • Termination - 5/16-18 Threaded Stud
Style	Female

Type Receptacle, Stud Type
UPC 783585458281

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating 150 A
Connectivity Threaded Stud
Current / Amperage Rating 150 A
Current Rating 150 A
Phase Single Phase
Voltage Rating Description 600V AC/DC
Wattage 90000

Conductor Related

Number Of Wires None
Wire Size #4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)

- National Electric Code (NEC), ANSI/NFPA 70
- UL and cUL Listed
- UL Enclosure Types 3R, 4X, 12

Nema Rating Non-NEMA

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - WDK H-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL15FRSW](#)