



# Single Pole Products, Male Inlet, Double Set Screw Termination, 150 Amp Series, Black

By Bryant  
Catalog # [HBL15MRBK](#)

Single Pole Products, Male Inlet, Double Set Screw Termination,  
150 Amp Series, Black



## General

Application	Extra Heavy Duty Industrial
Catalog Number	HBL15MRBK
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Performance	Electrical - Amperage Rating - 150A Maximum  Electrical - Voltage Ratings - 600V AC Maximum  250V DC Maximum  Mechanical - Product Identification - Ratings are a permanent part of device  Mechanical - Terminal Accommodation - #8 to #2 AWG
Series	Series 15
Style	Double Set Screw Male
Type	Receptacle
UPC	783585458120

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	150 A
Connectivity	Double Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

## Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

## Certifications And Compliance

Industry Standard(s)	National Electric Code (NEC), ANSI/NFPA 70  UL and cUL Listed  UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

- [Catalog Page - WDK H-3 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-HBL15MRBK-SPEC-EN | REV 6/2024