



Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20R, Screw Terminal, Orange

By Bryant
Catalog # 72120IG



Locking Devices, Isolated Ground, Industrial, Flush Nylon Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20R, Screw Terminal, Orange

Features

- Limits electrical noise on the equipment grounding circuit by providing two grounding paths for the installation
- Nylon deep face design
- Triple-wipe brass line contacts
- Ground contacts and ground termination
- Nickel and brass plated wrap-around steel yoke

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	72120IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786701243

Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Three Phase
Voltage Rating	120/208 V
Voltage Rating Description	3 Phase Y 120/208V AC
Wattage	

Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L21-20R
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY H-10 Catalog Page](#)
- [Catalog Page - BRY D-7 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-72120IG-SPEC-EN | REV 6/2024