



# Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20P, Screw Terminal, White

By Bryant  
 Catalog # 72120MB



Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, L21-20P, Screw Terminal, White

## General

Application	Extra Heavy Duty Industrial
Catalog Number	72120MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet Flanged Inlet
UPC	781786701267

## Dimensions

Dimensions	3.06 in x 3.06 in x 2.03 in
Display Size	Standard Sized Product
Height	2.03 in
Length	3.06 in
Width	3.06 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208V AC

## Conductor Related

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L21-20P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalog Page - BRY H-10 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-72120MB-SPEC-EN | REV 6/2024