



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Male to 6) Females, Distribution Block, 400A 600V AC/DC, Single Conductor, Pre-Wired



By Bryant  
Catalog # [HBL7DBGN](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male to 6) Females, Distribution Block, 400A 600V AC/DC, Single Conductor, Pre-Wired, Green

## Features

- Industrial Grade
- Male to 6) Females
- Distribution Block

## Application

High Ampacity

## Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

## General

Catalog Number	HBL7DBGN
Color	Green
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Distribution Block
Material	Brass and Elastomer
Number Of Pins	1) In, 6) Out- Male 6) Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16

## Specifications

Style  
Type  
UPC

- Body Material - Thermoplastic Elastomer
  - Contact Material - Brass
  - Product Type - Distribution Block
- 1-Male, 6-Female  
Distribution Block  
783585112381

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBL7DBGN](#)