



Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7310G

Locking Devices, Industrial, Flush Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black



Application

Extra Heavy Duty Industrial Specification Grade

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Receptacle-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Single Receptacle
Type	Receptacle
UPC	781786628021

Dimensions

Dimensions	3.28 in x 1.71 in x 1.14 in
Display Size	Standard Sized Product
Height	1.14 in
Length	3.28 in
Width	1.71 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-16 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7310G-SPEC-EN | REV 7/2023