



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male-Male, Tri-Tap, 400A 600V AC/DC, Single Conductor, Pre-Wired, Orange



By Bryant  
Catalog # [HBLF3MO](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male-Male, Tri-Tap, 400A 600V AC/DC, Single Conductor, Pre-Wired, Orange

### Features

- Industrial Grade
- Female-Male-Male-Male
- Tri-Tap

### Application

High Ampacity

### Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

### General

Catalog Number	HBLF3MO
Color	Orange
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Tri-Taps
Material	Brass and Elastomer
Number Of Pins	1) In, 3) Out- Male-Female-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

### Series Specifications

Style  
Type  
UPC

### Series 16

- Body Material - Thermoplastic Elastomer
  - Contact Material - Brass
  - Product Type - T's" and Tri-Taps
  - Tee and Tap Type - Tri-Tap 3-Fer Female-Male-Male-Male Tees and 3-Fers
- 783585112442

### Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

### Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

### Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLF3MO](#)