




Straight Blade Devices, Locking Devices, Bryant Midget Locking, Accessories, Weatherproof for Midget Connectors, For 15A Black

By Bryant
Catalog # [7460BC](#)



Straight Blade Devices, Locking Devices, Bryant Midget Locking, Accessories, Weatherproof for Midget Connectors, For 15A Black

Application

Heavy Duty Industrial

General

Environmental Conditions	For Weatherproofing Connectors
Item Type	Weatherproofing Boot for 2-Pole 2-Wire Non-Grounding Connectors
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Cord Mounted
OEM Brand Name	Hubbell Bryant
Style	For Midget Locking
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Weatherproof Boot
UPC	781786628717

Dimensions

Display Size	Midget NEMA Locking
Weight	0.05 lb

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant H-20 Catalog page](#)
[Catalog Page - Bryant A-28 Catalog page](#)
[Catalog Page - Bryant H-6 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7593NC - Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White](#)
[7400BCR - Straight Blade Devices, Locking Devices, Accessories, Weatherproof Boot for Midget Devices, For 15A, 2-Pole 2-Wire, Yellow](#)
[7468N - Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1R, Screw Terminal, Black](#)
[7486MB - Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3P, Screw Terminal, Black & White](#)
[7466N - Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1P, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7460BC-SPEC-EN | REV 7/2023