



# Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1P, Screw Terminal, Black

By Bryant  
Catalog # 7466N



Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1P, Screw Terminal, Black

## Application

Extra Heavy Duty Industrial

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786638518

## Dimensions

Dimensions	1.63 in x 1.38 in x 1.28 in
Display Size	Midget Locking
Height	1.28 in
Length	1.63 in
Width	1.38 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 V
Voltage Rating Description	125V

## Conductor Related

Number Of Wires	2-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	ML-1P
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[7464NB - Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black](#)

[7464N - Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, ML-1R, Screw Terminal, Black & White](#)

[7468N - Locking Devices, Bryant Midget Locking, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, ML-1R, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-7466N-SPEC-EN | REV 7/2023