



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female Receptacle, 300/400A 600V AC/DC, Single Conductor, ThreadedStud, White



By Bryant
Catalog # [HBLFRSW](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Female Receptacle, 300/400A 600V AC/DC, Single Conductor, ThreadedStud, White

Features

- Industrial Grade
- Female Receptacle
- 300/400A 600V AC/DC

Application

High Ampacity Connections

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #4 to 4/0 AWG

General

Catalog Number	HBLFRSW
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Panel Mount Receptacle
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Threaded Thru-Hole
Number Of Poles	1-Pole
Series	Series 16
Specifications	<ul style="list-style-type: none"> • Base Compound - Thermoplastic Elastomer • Contact Material - Brass • Mounting Hole - 4x Ø .20" • Retaining Screw Material - Nylon • Termination - 1/2-13 UNC-2A Threaded Stud

Style	Stud Type, Through Hole Mounting, Female
Type	Receptacle
UPC	783585112718

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	400 A
Connectivity	Stud Type
Current / Amperage Rating	400 A
Current Rating	400 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	240000

Conductor Related

Number Of Wires	1-Wire
Wire Size	#4 AWG to #4/0 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • National Electric Code (NEC), ANSI/NFPA 70 • UL and cUL Listed • UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	1575

Product Assets

[Catalog Page - WDK H-6 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)

