



Locking Devices, Locking Devices, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black and White

By Bryant
Catalog # 7506



Locking Devices, Industrial, Female Connector Body, 15A 125V,
2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black
and White

Application

Heavy Duty Industrial

General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786628939

Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard Sized Product
Height	2.78 in
Length	1.53 in
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG
Number Of Conductors	2-Pole Non-Grounding
Number Of Wires	2-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	L1-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7548 - Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black](#)

[7526 - Locking Devices, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White](#)

[SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Stainless Steel](#)

[P7BK - Wallplate, 1-Gang, 1.40" Opening, Black](#)

[7540 - Locking Devices, Industrial, Duplex Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7506-SPEC-EN | REV 7/2023