



Locking Devices, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White

By Bryant
Catalog # 7526



Locking Devices, Industrial, Flanged Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15P, Screw Terminal, White

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Flanged Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Type	Flanged Receptacle
UPC	781786629127

Dimensions

Dimensions	2.56 in x 2.19 in x 1.78 in
Display Size	Standard Sized Product
Height	1.78 in
Length	2.56 in
Width	2.19 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#14 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L1-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7540 - Locking Devices, Industrial, Duplex Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black](#)

[SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Stainless Steel](#)

[RW57300 - Wallplates and Boxes, Weatherproof Hood, 1-Gang, Multi Opening, Vertical, Gray](#)

[P7BK - Wallplate, 1-Gang, 1.40" Opening, Black](#)

[7548 - Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7526-SPEC-EN | REV 7/2023