



# Locking Devices, Flanged Inlet, 20A 250V, 2- Pole2-Wire Non-Grounding, Non-NEMA, Black

By Bryant  
Catalog # 8808MB



Locking Devices, Flanged Inlet, 20A 250V, 2-Pole 2-Wire Non-Grounding, NEMA L2-20, White

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## General

Catalog Number	8808MB
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786630789

## Dimensions

Dimensions 2.56 in x 2.56 in x 1.72 in

Display Size	Standard Sized Product
Height	1.72 in
Length	2.56 in
Width	2.56 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 V
Voltage Rating Description	250V

## Conductor Related

Number Of Wires	2-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L2-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-5 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 8808MB](#)