



# Single Pole Replacement Retaining Screw

By Bryant  
Catalog # [HBLRS](#)



SINGLE POLE REPLACEMENT RETAINING SCREW

## Application

High Ampacity

## General

Item Type	Replacement Parts
Material	Steel
Number Of Pins	Retaining Screw
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	<ul style="list-style-type: none"><li>• Electrical - Amperage Rating - 400A Maximum</li><li>• Electrical - Voltage Ratings - 600V AC Maximum</li><li>• 250V DC Maximum</li><li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li></ul>
Series	Series 16
Style	Replacement Retaining Screws
Type	Accessory
UPC	783585355610

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Voltage Rating Description	600V AC/DC

## Certifications and Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Logistics

Carton Quantity	500
-----------------	-----

## Product Assets

[Catalog Page - Bryant L-8 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Series 18 Single Pole 300 and 400 Amp Plugs](#)  
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-HBLRS-SPEC-EN | REV 7/2023