



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A, 600V AC/DC, Single Conductor, Pre-Wired



By Bryant  
Catalog # HBLTY

Heavy Duty Single Pole Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A, 600V AC/DC, Single Conductor, Pre-Wired

## Features

- Industrial Grade
- Female-Female-Male
- Tapping "Tee"

## Application

High Ampacity

## Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

## General

Catalog Number	HBLTY
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16

## Specifications

	• Body Material - Thermoplastic Elastomer
	• Contact Material - Brass
	• Product Type - T's" and Tri-Taps
	• Tee and Tap Type - "T" Fitting
Style	Tapping Tee Female-Female-Male
Type	Tees and 3-Fers
UPC	783585113203

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

## Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLTY](#)

