



Oh No!
IMAGE COMING SOON

IEC Pin and Sleeve, Splash Proof Angled Receptacle, 30/32 A, 200-415 VAC

By Bryant
Catalog # [BRY530AR6S](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Female, Receptacle, 30/32 A 200-415 VAC, 4-POLE 5-WIRE, Red, Splash Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	BRY530AR6S
Color	Red
Environmental Conditions	IP44
Ingress Protection	IP44
Insulation	Insulated Body
Material	PBT
Mounting Type	Screw Mount
Number Of Poles	4-POLE
Series	Splash Proof
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Angled Receptacle

UPC 781786785304

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Dielectric Strength	Withstand 3000V AC
Voltage - Maximum	600 VAC
Voltage Rating	200-415 VAC
Voltage Rating Description	200-415 VAC

Conductor Related

Number Of Wires	5-WIRE
Wire Size	#10 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	All constructions are UL Listed & cUL Listed, FileE14632, UL1686 Standard for Pin & Sleeve Configurations, VDE, CE
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Sales Drawings - M14042](#)
[Specifications - BRYANT_BRY530AR6S_spec](#)



A Hubbell brand