



# IEC Pin and Sleeve, Watertight Receptacle, 30/32 A, 200-415 VAC

By Bryant  
Catalog # [BRY530R6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Female, Receptacle, 30/32 A 200-415 VAC, 4-POLE 5-WIRE, Red, Watertight

## Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Color coded housings provide quick identification of mating devices

## Application

High Ampacity Connections

## General

Catalog Number	BRY530R6W
Color	Red
Environmental Conditions	IP67
Ingress Protection	IP67
Insulation	Insulated Body
Material	PBT
Mounting Type	Screw Mount
Number Of Poles	4-POLE
Series	Watertight IP67
Size	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Receptacle
UPC	781786782747



## Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Dielectric Strength	Withstand 3000V AC
Voltage - Maximum	600 VAC
Voltage Rating	200-415 VAC
Voltage Rating Description	200-415 VAC

## Conductor Related

Number Of Wires	5-WIRE
Wire Size	#10 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	All constructions are UL Listed & cUL Listed, FileE14632, UL1686 Standard for Pin & Sleeve Configurations, VDE, CE
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY K-4 Catalog Page](#)
- [Catalog Page - BRY K-5 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Sales Drawings - M14034](#)
- [Specifications - BRYANT\\_BRY530R6W\\_spec](#)



A Hubbell brand