



Locking Devices, Bryant Wiring Devices, Locking Devices, Industrial, Female Connector Body, 50A 125V, Non-NEMA

By Bryant
Catalog # CS6360



Locking Devices, Bryant Wiring Devices, Industrial, Female Connector Body, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Heavy Duty Black

Features

- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength
- Oversized contacts minimize operating temperature

Application

Heavy Duty Industrial

General

Catalog Number	CS6360
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Heavy Duty Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786639102

Dimensions

Dimensions	6.50 in x 2.56 in x 2.56 in
Display Size	Standard Sized Product
Height	2.56 in
Length	6.5 in
Width	2.56 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Conductor Range	#6 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-21 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CS6360](#)