



Locking Devices, Twist-Lock®, Economy, Male Plug, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6365L](#)



Economy Male Plug, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal

Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Male Nylon Plug
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	Replacement Part
Style	Heavy Duty
Type	Locking Plug
UPC	783585320694

Dimensions

Dimensions	6.38 in x 2.56 in x 2.56 in
Display Size	Standard Sized
Height	2.56 in
Length	6.38 in
Width	2.56 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalog Page - Bryant C-11 Catalog page](#)
[Catalog Page - Bryant L-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[CS6369L - Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[CS6364L - Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)
[7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS6365L-SPEC-EN | REV 7/2023