



# Net Select, Module, Fiber Adapter, With OFSP Bracket

By Bryant  
Catalog # [NSOFSB](#)

Net Select, Module, Fiber Adapter, With OFSP Bracket



## Features

- For use with Adapter Panels
- Snap mounts into structured cabling enclosures

## General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Fiber Adapter Bracket with OFSP
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Panel Bracket
UPC	883778502774

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• RoHS Compliant</li><li>• UL and cUL Listed</li></ul>
----------------------	--

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant R-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-NSOFSB-SPEC-EN | REV 7/2023