



# Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Steel

By Bryant  
Catalog # CS6377A



Locking Devices, Industrial, Flanged Inlet, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Heavy Duty Black

## Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

## General

Application	Extra Heavy Duty Industrial
Color	Metallic
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Male Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786253124

## Dimensions

Dimensions	2.77 in x 3.50 in x 3.50 in
Display Size	Standard Sized Product
Height	3.5 in
Length	2.77 in
Width	3.5 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 VAC
Voltage Rating Description	125V AC
Wattage	

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY H-21 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-CS6377A-SPEC-EN | REV 6/2024