



Trade Select, Switches and Lighting Controls, Vacancy Sensor Switch, 500W Max, 125V AC, Almond.

By Bryant
Catalog # [RMS100AL](#)



Trade Select, Switches and Lighting Controls, Vacancy Sensor Switch, 500W Max, 125V AC, Almond.

Application

1-Button

General

Catalog Number	RMS100AL
Control Output	Input Voltage
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	PIR= Red LED
Item Type	Residential Wall Switches
Load Capacity	500W Incandescent @ 120V AC
Material - Mounting Hardware	Screw Mounting
Operating Cycles	6,000 Cycles Minimum

Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Sensing Range	42 to 54 Inches above the Floor
UPC	883778112607

Electrical Ratings

Sensitivity	Adjustable W
Supply Voltage	120V AC V

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Specifications - RMS100AL](#)