



# Locking Devices, Industrial, Female Connector Body, 50A 480 V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant  
Catalog # [CS8464](#)

Locking Devices, Industrial, Female Connector Body, 50A 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

### Features

- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength
- Oversized contacts minimize operating temperature

### Application

Heavy Duty Industrial

### General

Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Heavy Duty Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786538191



### Dimensions

Dimensions	6.50 in x 2.56 in x 2.56 in
Display Size	Standard Sized Product
Height	2.56 in
Length	6.5 in
Width	2.56 in

### Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

### Conductor Related

Conductor Range	#6 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - BRY H-21 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.