



Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Zircon Sleeves, Green

By Bryant
Catalog # FSPLCQS3GN

Fiber Optic Panel Adapter, 12-Fiber, 3) LC Quad, Zircon Sleeves, Green



Features

- Premium Quality and High Performance Design

General

Adapter Type	LC Quad
Application	Interconnect
Catalog Number	FSPLCQS3GN
Color	Green
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) LC Quad
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620103846

Dimensions

Display Size	5.1" X 1.1"
--------------	-------------

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
	TIA-604-FOCIS

Logistics

Carton Quantity	4
-----------------	---

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPLCQS3GN-SPEC-EN | REV 6/2024