



# Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Green

By Bryant  
Catalog # [FSPLCQS6GN](#)

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Green



## Features

- Premium Quality and High Performance Design

## Application

Interconnect

## General

Color	<ul style="list-style-type: none"><li>• Green</li><li>• Green</li></ul>
EU RoHS Indicator	No
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	6) LC Quad
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Temperature Rating	-40C to +85C
UPC	662620103945

## Dimensions

Display Size 5.1" X 1.1"

## Electrical Ratings

Connectivity Receptacle  
Insertion Loss 0.30 dB  
Return Loss 55

## Conductor Related

Fiber Size 125 Micron  
Fiber Type Multimode

## Certifications and Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

## Logistics

Carton Quantity 4

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-FSPLCQS6GN-SPEC-EN | REV 7/2023