



# Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R



By Bryant  
Catalog # SP53IGOA

Circuit Watch Surge Suppression Straight Blade Receptacle,  
Industrial/Commercial Grade, Isolated Ground, 20A 125V, 2- Pole  
3-Wire Grounding, 5-20R, Orange

## Features

- Isolated Ground
- 20A 125V
- 2- Pole 3-Wire Grounding
- 5-20R
- Orange

## Application

IG Duplex with Light and Alarm

## General

Catalog Number	SP53IGOA
Color	Orange
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Style	Isolated Ground
Type	Duplex Receptacle

UPC 781786139176

## Dimensions

Display Size Standard

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications And Compliance

Nema Rating 5-20R

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - BRY D-2 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Power Disruption Solutions](#)
- [Literature - General Literature - Duplex Surge Receptacles](#)
- [Literature - General Literature - Surge Protection Devices](#)
- [Specifications - SP53IGOA](#)