



Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Bryant
Catalog # SP82A



Circuit Watch Surge Suppression Straight Blade Receptacle,
Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

General

Application	Duplex with Light and Alarm
Catalog Number	SP82A
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Hospital Grade
Style	Surge Protection Only
Type	Duplex Receptacle
UPC	781786139220

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY B-9 Catalog Page](#)
- [Catalog Page - BRY D-2 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Duplex Surge Receptacles](#)
- [Literature - General Literature - Surge Protection Devices](#)
- [Literature - General Literature - Healthcare Solutions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-SP82A-SPEC-EN | REV 6/2024