



Power Protection Products, GFCI Circuit Breaker Sensing Modules, Industrial, Auto Set, 240V AC, GFCI Circuit Breakers, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFMD240A](#)

Power Protection Products, GFCI Circuit Breaker Sensing Modules, Industrial, Auto Set, 240V AC, GFCI Circuit Breakers, 4-6 mA Trip Level, Black

Features

- Industrial
- Auto Set
- 240V AC
- GFCI Circuit Breakers
- 4-6 mA Trip Level

Application

Heavy Duty Industrial Commercial

General

Catalog Number	GFMD240A
Color	Black
EU RoHS Indicator	No
Enclosure Type	Toggle
Environmental Conditions	NEMA 4X with Supplied Gasket
Item Type	Auto Set Sensing Module
Material	Composite
Number Of Poles	None
OEM Brand Name	Hubbell Bryant
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Industrial
Type	Auto Reset
UPC	781786450011



Dimensions

Height	2.3 in
Length	4.7 in

Electrical Ratings

Amperage Rating	1-50 A
Connectivity	None
Current / Amperage Rating	1-50 A
Frequency Rating	80% of Full Rating Continuous
Phase	60Hz
Trip Range	.025 Seconds in
Trip Type	Standard
Voltage Rating	240 VAC
Voltage Rating Description	240 VAC

Conductor Related

Wire Size	Terminal Screws
-----------	-----------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Literature - General Literature - Ground Fault Sensing Module Specifications - GFMD240A](#)