



Power Protection Products, GFCI Circuit Breakers, Industrial, Double Pole, 50A 240V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFMDCB240502P](#)



Power Protection Products, GFCI Circuit Breakers, Industrial, Double Pole, 50A 240V AC, GFCI Circuit Breaker Sensing Modules, 4-6 mA Trip Level, Black

Features

- Industrial
- Double Pole
- 50A 240V AC
- GFCI Circuit Breaker Sensing Modules
- 4-6 mA Trip Level

Application

Heavy Duty Industrial Commercial

General

Catalog Number	GFMDCB240502P
Color	Black
EU RoHS Indicator	No
Enclosure Type	Toggle
Environmental Conditions	NEMA 4X with Supplied Gasket
Frame	Single Phase
Item Type	Circuit Breaker
Material	Composite
Number Of Poles	None
OEM Brand Name	Hubbell Bryant
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Industrial
Style	2 Pole
Timing Response	1-Pole
Type	Circuit Breaker

UPC 781786450455

Dimensions

Width 0.73 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	None
Current / Amperage Rating	50 A
Current Rating	50 A
Frequency Rating	80% of Full Rating Continuous
Interrupt Rating	50 A
Phase	60Hz
Trip Range	.025 Seconds in
Trip Type	Standard
Voltage Rating	240 VAC
Voltage Rating Description	240 VAC

Conductor Related

Wire Size Terminal Screws

Logistics

Carton Quantity 12

Product Assets

[Literature - General Literature - Ground Fault Sensing Module Specifications - GFMDCB240502P](#)