



Portable GFCI Plug, Manual Set, 15A, Black

By Bryant
Catalog # [GFPST15MA](#)



Circuit Guard® Heavy Duty Plugs Portable GFCI, Manual Set, 15A, Black

*Representative Image

Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Application

Outdoor/Indoor

General

Catalog Number	GFPST15MA
Color	Black
Environmental Conditions	NEMA 3R
Material	Polycarbonate
Number Of Poles	2
Series	GFCI
Style	Field Wired
Temperature Rating	-30°F (-35°C) - 150°F (66°C)
Type	Portable GFCI

UPC 783585694344

Electrical Ratings

Amperage Rating	15 A
Phase	Single
Voltage Rating	120 V
Wattage	1800 W

Conductor Related

Number Of Wires 3

Certifications And Compliance

Industry Standard(s)	cULus 943
Nema Rating	5-15

Product Assets

- [Installation Manuals - PD3068](#)
- [Sales Drawings - M14747](#)
- [Specifications - GFPST15MA](#)
- [Warranty - Industrial & Commercial Products](#)