



Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond, US Product

By Bryant
Catalog # [GFRST15LAU](#)



Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond, US Product

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction

General

| | |
|-------------------|---|
| Catalog Number | GFRST15LAU |
| Color | Light Almond |
| EU RoHS Indicator | Contact Manufacturer |
| Series | Heavy Duty |
| Specifications | <ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass |
| Style | Assembled In USA |

| | |
|------|--------------|
| Type | Standard |
| UPC | 883778124167 |

Electrical Ratings

| | |
|----------------------------|-------|
| Current / Amperage Rating | 15 A |
| Voltage Rating Description | 125 V |

Certifications And Compliance

| | |
|--------------------------|---|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating | 5-15R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - WDK K-5 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - GFRST15LAU](#)