



Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond, US Product

By Bryant
Catalog # [GFRST15LAU](#)



Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond, US Product

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction

General

Catalog Number	GFRST15LAU
Color	Light Almond
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass

Style	Assembled In USA
Type	Standard
UPC	883778124167

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-5 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - GFRST15LAU](#)