

IEC Pin and Sleeve

20 A, 3 Phase 600 VAC, 3-POLE, 4-WIRE

Plug

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection




Ordering Information

| Description | Series | Color | UPC Number | Catalog Number |
|---|-----------------|-------|--------------|------------------|
| Heavy Duty Products, IEC Pin and Sleeve | Watertight IP67 | Black | 781786782044 | BRY420P5W |

Listings

All constructions are UL Listed & cUL Listed
 File E14633
 UL1686 Standard for Pin & Sleeve Configurations
 CE



Specifications

| | |
|-------------|---------------------------|
| Application | High Ampacity Connections |
| Connection | Pressure Screw Terminal |
| Wire Size | #14AWG to #12AWG |
| Material | PBT |
| Mounting | Cord Mounted |

Performance

| Electrical | |
|-------------------------|---|
| Dielectric Voltage | Withstand 3000V AC |
| Max. Working Voltage | 600V AC RMS |
| Mechanical | |
| Impact Resistance | Per CSA C22.2 No. 182.1 / UL1682 |
| Product Identification | Identification and ratings are marked on device housing |
| Terminal Identification | Terminals identified in accordance with North American and IEC conventions |
| Environmental | |
| Flammability | HB |
| Ingress Protection | IP67 |
| Moisture Resistance | IEC 60309-1 |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |

Complementary Products

Complementary Products

Closure Cap

Online Resources

Customer Sales Drawings
 eCatalog