

# Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, White

By Bryant  
Catalog # [HBL15FRW](#)



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, White

## Features

- Double Set Screw Termination
- 150 Amp Series
- White

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

## General

Catalog Number	HBL15FRW
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none"> <li>• Base Compound - Thermoplastic Elastomer (TPE)</li> <li>• Contact Material - Brass</li> <li>• Mounting Hole - 3x Ø .20"</li> <li>• Retaining Screw Material - Nylon</li> <li>• Termination - (2) 5/32 Socket Head Set Screws</li> </ul>
Style	Double Set Screw Female

Type Receptacle, Stud Type  
UPC 783585458182

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating 150 A  
Connectivity Double Set Screw  
Current / Amperage Rating 150 A  
Current Rating 150 A  
Phase Single Phase  
Voltage Rating Description 600V AC/DC  
Wattage 90000

## Conductor Related

Number Of Wires None  
Wire Size #4 AWG Type SC/PPC Wire

## Certifications And Compliance

Industry Standard(s)

- National Electric Code (NEC), ANSI/NFPA 70
- UL and cUL Listed
- UL Enclosure Types 3R, 4X, 12

Nema Rating Non-NEMA

## Logistics

Carton Quantity 25  
Pallet Quantity 4500

## Product Assets

[Catalog Page - WDK H-3 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Single Pole Devices](#)  
[Specifications - HBL15FRW](#)