



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female Receptacle, 300/400A 600V AC/DC, Single Conductor, Threaded Mounting Holes

By Bryant
Catalog # [HBLFRSCBL](#)



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female Receptacle, 300/400A 600V AC/DC, Single Conductor, Threaded Mounting Holes, Stud Termination, Blue

Application

High Ampacity Connections

General

Color	Blue
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Panel Mount Receptacle
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Threaded Thru-Hole
Number Of Poles	1-Pole
Performance	<ul style="list-style-type: none">• Electrical - Amperage Rating - 400A Maximum• Electrical - Voltage Ratings - 600V AC Maximum• 250V DC Maximum• Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17• Mechanical - Product Identification - Ratings are a permanent part of device• Mechanical - Terminal Accommodation - #4 to 4/O AWG
Series	Series 16
Style	Stud Type, Threaded Hole Mounting, Female
Type	Receptacle
UPC	783585093611

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	400 A
Connectivity	Stud Type
Current / Amperage Rating	400 A
Current Rating	400 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	240000

Conductor Related

Number Of Wires	1-Wire
Wire Size	#4 AWG to #4/O AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
----------------------	--

Nema Rating Non-NEMA

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Bryant L-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBLFRSCBL-SPEC-EN | REV 7/2023