



Net Select, Module, 8-Way Coax, 2.3GHz, Plastic

By Bryant
Catalog # NSOVM82G



Net Select, Module, 8-Way Coax, 2.3GHz, Plastic

Application

- CATV

General

Catalog Number	NSOVM82G
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	8-Way Coax, 2.3GHz
Material - Mounting Hardware Specifications	Screw Mounting <ul style="list-style-type: none">Dimensions - 6.47 in. W x 2.09 in. H x 3.20 in. DMaterial - High impact plastic
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter
UPC	883778504419

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">RoHS CompliantUL and cUL Listed
----------------------	--

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - PREM S8 CatalogPage](#)
[Catalog Page - BRY R-5 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - NSOVM82G](#)